

Instrumentation Solutions for Hydrogen Applications

Components and systems for use with gaseous and liquid hydrogen



ENGINEERING YOUR SUCCESS.

Contents

On-Board Vehicles - EC-79 Certified Components

 Applications from 30 to 350 bar (435 - 5,076 ps Two Ferrule Tube Fittings - A-LOK[®] Series
 Applications up to 700 bar (10,152 psi)
 Medium Pressure Fittings - Cone and Thread Medium Pressure Needle Valves SM Series - Medium Pressure Tubing - Autoclave Engineer

ISO 19880-3 Certified Products for Hydrogen Refueling Stations

Medium Pressure Needle Valves 20SM Serie Medium Pressure O-Ring Check Valves CXO

General Hydrogen Applications

Applications up to 414 bar (6,000 psi)..... Two Ferrule Tube Fittings - A-LOK[®] Series ... Single Ferrule Tube Fittings - CPI[™] Series ... Needle Valves - H Series Ball Valves - B Series - Isolation and Direction Proportional Relief Valves - HPRV Series Inline Filters - F Series Check Valves - CO Series - Directional Control Stream Switching Systems - R-Max[™] Gen II S Modular Sample Conditioning Systems - Intra Pressure Regulators - IR4000 and IR6000 Ser Excess Flow Shutoff Valves - FS190 Series... Applications up to 1,380 bar (20,000 psi)...... Medium Pressure Two Ferrule Inverted Tube Medium Pressure Fittings - Cone and Thread Permanent Ferrule-less Connectors - Phastit Ball Valves - Hi-Pro Series - Isolation Valves. Ball Valves - HB Series - Isolation Valves Needle Valves MAN - MPI[™] Series Medium Pressure Needle Valves 15SM and 20 Medium Pressure O-Ring Check Valves CXO Medium Pressure O-Ring Check Valves MAC Double Block & Bleed Needle Type Manifold Relief Valves - Soft Seat RVS Series - Autocla Medium Pressure Tubing - MPI[™] Series...... Medium Pressure Actuators - Autoclave Engin Medium Pressure Adapters - Autoclave Engin Medium Pressure Accessories - Autoclave Er

Cryogenic/LH₂ Applications

Manual Globe Valves - Stainless Steel - Besto Manual Globe Valves - Stainless Steel - Besto Pneumatically Actuated Globe Valves - Stainle Safety Relief Valves - Stainless Steel - Bestob Lift Check Valves - Stainless Steel - Bestobell Swing Check Valves - Stainless Steel - Bestob Manual Gate Valves - Stainless Steel - Bestob Actuated Gate Valves - Stainless Steel - Pneu

WARNING

FAILURE, IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS AND/OR SYSTEMS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker Hannifin Corporation, its subsidiaries or its authorized distributors provide product and/or system options for further investigation by users having technical expertise. It is important that you analyze all aspects of your application and review the information concerning the product or system in the current product catalog. Due to the variety of operating conditions and applications for these products or systems, the user, through its own analysis and testing, is solely responsible for making the final selection of the products and assuring that all performance, safety and warning requirements of the application are met. The products described herein, including without limitation, product features, specifications, designs, availability and pricing, are subject to change by Parker Hannifin Corporation and its subsidiaries at any time without notice.

Offer of Sale

The items described in this document are available for sale by Parker Hannifin Corporation, its subsidiaries or its authorized distributors. Any sale contract entered into by Parker will be governed by the provisions stated in Parker's standard terms and conditions of sale (copy available upon request).

SI)	6
	6
	7
- Autoclave Engineers®	
Autoclave Engineers®	
ers®	7

es - Autoclave Engineers [®]	8
Series - Autoclave Engineers®	8

	10
	-
nal Control Valves	
ol Valves Series	
aFlow™ Series	
ries	
	12
Fittings - MPI™ Series Parlen Ante alena Facilia com®	
- Parker Autoclave Engineers [®] e [®] Series	
	13
0SM Series - Autoclave Engineers®	
Series - Autoclave Engineers [®] - MPI™ Series	
- MPT ^{am} Series - Autoclave Engineers [®]	
ve Engineers [®]	
~	
neers®	
eers®	
ngineers®	15

bell Industrial	16
bell Marine	16
ess Steel - Bestobell Marine	16
cell Industrial	16
I Marine	17
bell Industrial	17
bell Industrial	17
Imatic Tyre Design - Bestobell Industrial	17

Your Reliable Partner for Driving the **Energy Evolution Forward**

Parker is supporting the global decarbonization efforts through a broad range of solutions for a variety of applications. Our hydrogen-compatible components and systems enable safe and efficient operation from vacuum to 1,380 bar (20,000 psi) and temperatures from -253°C to +538°C (-423°F to +1000°F).



1,380 BAR 20,000 PSI

Parker's needle valves 20SM series and check valves CXO series have successfully passed all the required tests for high pressure gas valves used in gaseous hydrogen stations of up to the H70 designation specified in ISO 19880-3 certification.



ON-BOARD VEHICLES

Two Ferrule Tube Fittings - A-LOK® Series EC-79 Certified Parker Autoclave Engineers®: Medium Pressure Fittings EC-79 Certified Needle Valves - SM Series EC-79 Certified Medium Pressure Tubing EC-79 Certified

GENERAL HYDROGEN APPLICATIONS

Two Ferrule Tube Fittings - A-LOK® Series Single Ferrule Tube Fittings - CPI[™] Series Needle Valves - H. V Series Permanent Ferrule-less Connectors - Phastite® Series Ball Valves - B, Hi-Pro, HB Series Proportional Relief Valves - HPRV Series Inline Filters - F Series **Check Valves - CO Series** Stream Switching Systems - R-Max II Modular Sample Conditioning Systems - IntraFlow[™] Series Pressure Regulators - IR4000 and IR6000 Series Excess Flow Shutoff Valves - FS190 Series

CRYOGENIC/LH, APPLICATIONS

Bestobell Cryogenic Valves: Manual Globe Valves Pneumatically Actuated Globe Valves Safety Relief Valves Lift Check Valves Swing Check Valves Manual Gate Valves **Actuated Gate Valves**

VACUUM

Parker's range of tube fittings, needle valves and tubing for pressures up to 700 bar meet the general requirements of hydrogen components and systems used on hydrogen-powered motor vehicles as per regulation (EC) No 79/2009 of The European Parliament and of The Council of 14 Jan 2009

ISO-CERTIFIED PRODUCTS FOR REFUELING STATIONS

Parker Autoclave Engineers®: Needle Valves - 20SM Series ISO 19880-3 Certified Check Valves - CXO Series ISO 19880-3 Certified

GENERAL HYDROGEN APPLICATIONS

Parker Autoclave Engineers®:

Medium Pressure Fittings - Cone and Thread Needle Valves - 15SM and 20SM Series Check Valves - CXO Series Double Block & Bleed Needle Type Manifold - 20DBNV Series **Relief Valves - RVS Series** Medium Pressure Accessories and Adapters Medium Pressure Actuators

Medium Pressure MPI[™] Series:

Fittinas Tubina Needle Valves - MAN Series Check Valves - MAC Series

> Hydrogen can be very damaging to most metallic materials, causing embrittlement cracking. Follow this link to learn about the factors which can cause hydrogen embrittlement: https://discover.parker.com/Challenge-of-Hydrogen-Embrittlement-White-Paper





Stainless Steel material is Parker's standard offering for hydrogen systems and all the pressure and temperature ratings featured in this catalogue refer to this grade. Other materials are available on request.



On-Board Vehicles

Components for on-board hydrogen-powered vehicles for pressures from 30 to 700 bar (435 to 10, 152 psi). **EC-79** Certified

Parker's range of products approved for use on-board hydrogen-powered vehicles from 30 to 700 bar includes tube fittings, needle valves and tubing. These products meet the general requirements of hydrogen components and systems used on hydrogen-powered motor vehicles as per regulation (EC) No 79/2009 of The European Parliament and of The Council of 14 Jan 2009.

Applications from 30 to 350 bar (435 - 5,076 psi)



Two Ferrule Tube Fittings - A-LOK® Series EC-79 Certified

Parker A-LOK® two ferrule tube fittings are designed to achieve quality leak-free connections on-board hydrogen-powered vehicles up to 350 bar pressures and temperatures down to -40°C. These fittings provide reliable operation in cryogenic, pressure & thermal cycling and vibration applications. Manufactured at an IATF 16949 certified plant and EC-79 approved for hydrogen service, they come in a range of sizes and configurations in 316 Stainless Steel material. For optimised installation instructions see p.18 of this catalogue.

To order EC-79 certified components, simply add the suffix EC79 at the end of your part number.

For more details please see catalogue ref. 4190-FMTG.

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1" (6mm to 25mm)*	350 bar (5,076 psi)	-40°C to +120°C (-40°F to +248°F)	Gas, Liquid	4190-FMTG

*A-LOK® tees and crosses approved in sizes up to 1/2" (12mm). Please contact Parker for further information.



Applications up to 700 bar (10, 152 psi)



Engineers[®] **EC-79** Certified

number.

For more details please see catalogue ref. 02-0124SE.

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1"	700 bar (10,152 psi)	-40°C to +120°C (-40°F to +248°F)	Gas, Liquid	02-0124SE

Engineers® EC-79 Certified

Parker Autoclave Engineers SM Series valves are designed specifically for use with matching orifice medium pressure cone & thread fittings and tubing for the most efficient flow path possible using cone & thread style connections. They are manufactured using high tensile strength UNS S31600/S31603 cold worked 316/316L Stainless Steel material as standard for 700 bar (10,152 psi) MAWP. To order EC-79 certified components, simply add the suffix HYGEC79 at the end of your part number.

For more details please see catalogue ref. 02-0112SE.

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1"	700 bar (10,152 psi)	-40°C to +120°C (-40°F to +248°F)	Gas	02-0112SE

Medium Pressure Tubing - Autoclave Engineers® **EC-79** Certified

Parker Autoclave Engineers offers a complete selection of austenitic, cold drawn stainless steel tubing designed to match the performance standards of Parker Autoclave valves and fittings. Parker Autoclave Engineers medium pressure tubing is manufactured specifically for high pressure applications requiring both strength and corrosion resistance. For more details please see catalogue ref. 02-0124SE.

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1"	700 bar (10,152 psi)	-40°C to +120°C (-40°F to +248°F)	Gas, Liquid	02-0124SE
		7		

Medium Pressure Fittings - Cone and Thread - Autoclave

Parker Autoclave Engineers medium pressure cone and thread connections are designed for applications that require higher flow rate capability. Manufactured from high tensile strength cold worked 316 Stainless Steel material as standard for 700 bar (10, 152 psi) MAWP, this Medium Pressure range has all the benefits of the High Pressure version with all metal sealing for operations at temperatures from -40°C to +120°C (-40°F to +248°F).

These fittings are designed for use with Parker Autoclave Engineers' 20SM Series valves and medium pressure tubing according to ASME B31.3 Chapter IX standards.

To order EC-79 certified components, simply add the suffix EC79 at the end of your part

Medium Pressure Needle Valves SM Series - Autoclave

ISO Products For H₂ Refueling Stations Components for hydrogen refueling stations for pressures up to

700 bar (10,152 psi). ISO 19880-3 Certified

Parker's needle and check valves have successfully passed the required tests for high pressure valves used in gaseous hydrogen stations as specified in ISO 19880-3 certification.



Medium Pressure Needle Valves 20SM Series - Autoclave **Engineers**[®] ISO 19880-3 Certified

These Parker Autoclave Engineers 20SM Series Needle Valves (HYG option) have unique STEM/SEAT and PACKING design that can withstand temperatures ranging between -73°C and 316°C and pressures of up to 700 bar (10,152 psi).

The valves are available with two different styles of connection options including cone & thread and MPI[™].

To order ISO 19880-3 certified components, simply add the suffix HYG at the end of your part number.

For more details please see catalogue ref. 02-0112SE.

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1"	700 bar (10,152 psi)	-73°C to +316°C (-99°F to +601°F)	Gas	02-0112SE



Medium Pressure O-Ring Check Valves CXO Series - Autoclave **Engineers**[®] ISO 19880-3 Certified

These Parker Autoclave Engineers O-Ring Check Valves CXO Series (HYG option) can withstand temperatures ranging between -73°C and 316°C and pressures of up to 1,380 bar (20,000 psi).

The valves are available with two different styles of connection options including cone & thread and MPI[™].

To order ISO 19880-3 certified components, simply add the suffix HYG at the end of your part number.

For more details please see catalogue ref. 02-0124SE.

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1"	700 bar (10,152 psi)	-73°C to +316°C (-99°F to +601°F)	Gas	02-0124SE



General Hydrogen Applications

Components for general hydrogen applications at pressures from vacuum to 1,380 bar (20,000 psi).

Parker offers an extensive range of high-quality components and system solutions suitable for general hydrogen use in a wide variety of industries including power generation, petrochemical, agricultural and research & development.

Applications up to 414 bar (6,000 psi)



Two Ferrule Tube Fittings - A-LOK® Series

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/16" to 2" (2mm to 50mm)	414 bar (6,000 psi)*	-253°C to +538°C (-423°F to +1000°F)**	Gas, Liquid	4190-FMTG
* 51 () 5 (/C.1.1. 1.1. 1.1	1 000 1

Please refer to Parker tube tables for higher pressure tube/fitting combinations up to 689 bar (10,000 psi).

** Material de-rating and media compatibility factors need to be taken into consideration for higher temperature applications.

For optimised installation instructions see p.18 of this catalogue.



Single Ferrule Tube Fittings - CPI[™] Series

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1" (6mm to 25mm)	414 bar (6,000 psi)	-253°C to +538°C (-423°F to +1000°F)*	Gas, Liquid	4190-FMTG

*Material de-rating and media compatibility factors need to be taken into consideration for higher temperature applications.



Needle Valves - H Series

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" - 1" (6mm-12mm)	414 bar (6,000 psi)	-54°C to +538°C (-65°F to +1000°F)	Gas	4190-VMS



vailable Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/8" to 3/4" 3mm to 18mm)	345 bar (5,000 psi)	-54°C to +232°C (-65°F to +450°F)	Gas	4110-NV

(3r

Av

Ball Valves - B Series - Isolation and Directional Control Valves

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/8" to 3/4" (3mm to 18mm)	414 bar (6,000 psi)	-54°C to +232°C (-65°F to +450°F)	Gas	4121-BV



Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" (6mm)	414 bar (6,000 psi)	-57°C to +204°C (-70°F to +399°F)	Gas	4190-HPRV



Learn more:

www.parker.com/hydrogen-service

Needle Valves - V Series - Isolation and Flow Control Valves

Proportional Relief Valves - HPRV Series

MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
414 bar 6,000 psi)	-51°C to +204°C (-60°F to +399°F)	Gas	4135-CV



Check Valves - CO Series - Directional Control Valves

A	vailable Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
((1/4" to 1/2" 6mm to 12mm)	414 bar (6,000 psi)	-57°C to +204°C (-71°F to +399°F)	Gas	4135-CV



Stream Switching Systems - R-Max[™] Gen II Series

Available Size	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/8"	34 bar (500 psi)	-57°C to +204°C (-71°F to +399°F)	Gas	4141-R



Modular Sample Conditioning Systems - IntraFlow™ Series	

Available Size	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/8"	34 bar (500 psi)	-57°C to +204°C (-71°F to +399°F)	Gas	4250



Pressure Regulators - IR4000 and IR6000 Series

Available Size	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4"	276 bar (4,000 psi)	-40°C to +260°C (-40°F to +500°F)	Gas	4255-PA



Excess Flow Shutoff Valves - FS190 Series

A	vailable Size	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
	1/4"	241 bar (3,500 psi)	-23°C to +66°C (-9°F to +151°F)	Gas	4255-PA

Applications up to 1,380 bar (20,000 psi)



Medium Pressure T Series

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1"	1,034 bar (15,000 psi)	-253°C to +538°C (-423°F to +1000°F)*	Gas, Liquid	4234-MA

* Material de-rating and media compatibility factors need to be taken into consideration for higher temperature applications.

Medium Pressure Engineers®

1/4" to 1 1/2" 1,380 bar (20,000 psi)* -253°C to +538°C (-423°F to +1000°F)* Gas, Liquid 02-0124SE	Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
	1/4" to 1 1/2"	,		Gas, Liquid	02-0124SE

* Material de-rating and media compatibility factors need to be taken into consideration for higher temperature and higher pressure applications. Refer to technical catalogue 02-0142SE.

Permanent Ferrule-less Connectors - Phastite[®] Series

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1" (6mm to 25mm)	1,380 bar (20,000 psi)	-45°C to +93°C (-49°F to +199°F)	Gas	4235-PH





Ball Valves - HB Series - Isolation Valves

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/8" to 1/2" (6mm to 12mm)	689 bar (10,000 psi)	-54°C to +204°C (-65°F to +399°F)	Gas	4121-BV



Medium Pressure Two Ferrule Inverted Tube Fittings - MPI™

Medium Pressure Fittings - Cone and Thread - Parker Autoclave

Ball Valves - Hi-Pro Series - Isolation Valves

MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
689 bar 0,000 psi)	-54°C to +232°C (-65°F to +450°F)	Gas	4190-HBV



Needle Valves MAN - MPI[™] Series

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1"	1,034 bar (15,000 psi)	-73°C to +316°C (-99°F to +601°F)	Gas	4234-MA

This valve has been modified for use with Hydrogen. To order, add the suffix HYG at the end of your part number.



Medium Pressure Needle Valves 15SM and 20SM Series -**Autoclave Engineers®**

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1 1/2"	1,380 bar (20,000 psi)*	-73°C to +316°C (-99°F to +601°F)*	Gas	02-0112SE

This valve has been modified for use with Hydrogen. To order, add the suffix HYG at the end of your part number.



Medium Pressure O-Ring Check Valves CXO Series - Autoclave **Engineers**®

Availabl	e Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" t	to 1"	1,380 bar (20,000 psi)*	-73°C to +316°C (-99°F to +601°F)*	Gas	02-0124SE

This valve has been modified for use with Hydrogen. To order, add the suffix HYG at the end of your part number.

Medium Pressure O-Ring Check Valves MAC - MPI[™] Series

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1"	1,034 bar (15,000 psi)	-73°C to +316°C (-99°F to +601°F)	Gas	4234-MA

This valve has been modified for use with Hydrogen. To order, add the suffix HYG at the end of your part number.



Double Block & Bleed Needle Type Manifold - 20DBNV Series -**Autoclave Engineers®**

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 9/16"	1,380 bar (20,000 psi)*	-73°C to +316°C (-99°F to +601°F)*	Gas	02-9328SE

This valve has been modified for use with Hydrogen. To order, add the suffix HYG at the end of your part number.

* Material de-rating and media compatibility factors need to be taken into consideration for higher temperature and higher pressure applications. Refer to technical catalogue 02-0142SE.



Relief Valves - Soft Seat RVS Series - Autoclave Engineers®

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
9/16"	1,380 bar (20,000 psi)	0°C to +204°C (32°F to +399°F)	Gas	02-0129SE

number.

Medium Pressure Tubing - MPI[™] Series

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1"	1,034 bar (15,000 psi)	-253°C to +538°C (-423°F to +1000°F)	Gas, Liquid	4234-MA

Medium Pressure Actuators - Autoclave Engineers®

Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
1/4" to 1 1/2"	1,380 bar (20,000 psi)	-73°C to +316°C (-99°F to +601°F)	Gas, Liquid	02-0121SE





* Material de-rating and media compatibility factors need to be taken into consideration for higher temperature applications.

This valve has been modified for use with Hydrogen. To order, add the suffix HYG at the end of your part

Medium Pressure Adapters - Autoclave Engineers®

MWP	Temperature	Hydrogen Form	Catalogue Ref. Number	
1,379 bar (20,000 psi)	-253°C to +538°C (-423°F to +1000°F)*	Gas, Liquid	02-0127SE	

Medium Pressure Accessories - Autoclave Engineers®

MWP	Temperature	Hydrogen Form	Catalogue Ref. Number	
1,380 bar (20,000 psi)	-253°C to +538°C (-423°F to +1000°F)*	Gas, Liquid	02-0134SE	

Cryogenic/LH₂ Applications Components for cryogenic/LH₂ applications at temperatures down to -253°C (-423°F) and pressures up to 50 bar (725 psi).

Designed and engineered for use with Group 1 gases, Parker Bestobell's valves are suitable for liquid hydrogen applications requiring temperatures as low as -253°C. All valves are pressure-tested prior to dispatch.

To order, add the suffix -H at the end of your part number.



Manual Globe Valves - Stainless Steel - Bestobell Industrial

Available Connections	Seat Type	Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
Butt Weld Socket Weld Flange Class 150 and 300	Soft	DN15 to DN100 (1/2" to 4")	Up to 50 bar (725 psi)	-253°C to +65°C (-423°F to +149°F)	Gas	5190-BBV



Manual Globe Valves - Stainless Steel - Bestobell Marine

Available Connections	Seat Type	Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
Butt Weld Socket Weld Flange Class 150 and 300	Metal to Metal	DN15 to DN100 (1/2" to 4")	Up to 50 bar (725 psi)	-253°C to +80°C (-441°F to +176°F)	Gas, Liquid	5190-BBM



Pneumatically Actuated Globe Valves - Stainless Steel -**Bestobell Marine**

Available Connections	Seat Type	Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
 Butt Weld Socket Weld Flange Class 150 and 300 	Metal to Metal	DN15 to DN100 (1/2" to 4")	Dependent on end connections/ actuator	-253°C to +80°C (-423°F to +176°F)	Gas, Liquid	5190-BBM



Safety Relief Valves - Stainless Steel - Bestobell Industrial

Available Connections	Seat Type	Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
Various Contact Parker	Soft	DN10, DN15, DN20 (11.4, 14.0, 20.5 mm)	Up to 30 bar (435 psi)	-253°C to +65°C (-423°F to +149°F)	Gas	5190-BBV



Lift Check Valves - Stainless Steel - Bestobell Marine

Available Connections	Seat Type	Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
Butt Weld Socket Weld Flange Class 150 and 300	Soft	DN15 to DN100 (1/2" to 4")	Up to 50 bar (725 psi)	-253°C to +80°C (-423°F to +176°F)	Gas, Liquid	5190-BBM



Swing Check Valves - Stainless Steel - Bestobell Industrial

Available Connections	Seat Type	Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
• Butt Weld • Socket Weld • Flange Class 150 and 300	Soft	DN25 to DN80 (1" to 3")	Up to 50 bar (725 psi)	-253°C to +65°C (-423°F to +149°F)	Gas, Liquid	5190-BBV



Manual Gate Valves - Stainless Steel - Bestobell Industrial

Seat Type	Avai
Soft	DN4 (1



Actuated Gate Valves - Stainless Steel - Pneumatic Tyre Design - Bestobell Industrial

Available Connections	Seat Type	Available Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
Butt Weld Socket Weld	Soft	DN40 to DN100 (1 1/2" to 4")	Up to 40 bar (580 psi)	-253°C to +65°C (-423°F to +149°F	Gas	5190-BBV

vailable Sizes	MWP	Temperature	Hydrogen Form	Catalogue Ref. Number
DN40 to DN100 (1 1/2" to 4")	Up to 40 bar (580 psi)	-253°C to +65°C (-423°F to +149°F	Gas	5190-BBV

Appendix

A-LOK® tube fittings installation for hydrogen service

Parker has an improved and optimised installation procedure for its A-LOK[®] parts used in hydrogen service. Please follow the steps below for correct installation.

1. The tube should be fully inserted into the shoulder of the fitting until full tube abutment is achieved.

2. The nut should be advanced to the finger tight position and then be marked at the 6 o'clock position.

3. The nut should then be advanced 1 ½ turns with the appropriate wrench making sure a back-up wrench is used to hold the fitting body during the tightening process. 4. The mark will now be at the 12 o'clock position.

Once this has been achieved, the assembly will be ready to use in your Hydrogen system. For tube specifications, ordering information, preparation and pressure ratings, please refer to the Parker Fittings, Materials and Tubing Guide catalogue ref. 4190-FMTG.

Worldwide Division Headquarters

Europe, Middle East, Africa

AE – **United Arab Emirates,** Dubai Tel: +971 4 8127100

AT – Austria, St. Florian Tel: +43 (0)7224 66201

AZ – Azerbaijan, Baku Tel: +994 50 2233 458

BE/NL/LU – Benelux, Hendrik Ido Ambacht Tel: +31 (0)541 585 000

BY – Belarus, Minsk Tel: +48 (0)22 573 24 00

CH – **Switzerland,** Etoy Tel: +41 (0)21 821 87 00

CZ – Czech Republic, Prague Tel: +420 284 083 111

DE – Germany, Kaarst Tel: +49 (0)2131 4016 0

DK – Denmark, Ballerup Tel: +45 43 56 04 00

ES – Spain, Madrid Tel: +34 902 330 001

FI – Finland, Vantaa Tel: +358 (0)20 753 2500

FR – France, Contamine s/Arve Tel: +33 (0)4 50 25 80 25

GR – Greece Tel: +30 69 44 52 78 25

HU – Hungary, Budaörs Tel: +36 23 885 470

IE – **Ireland,** Dublin Tel: +353 (0)1 466 6370

IL – Israel Tel: +39 02 45 19 21

IT – Italy, Corsico (MI) Tel: +39 02 45 19 21

KZ – Kazakhstan, Almaty Tel: +7 7273 561 000

NO – Norway, Asker Tel: +47 66 75 34 00

PL – Poland, Warsaw Tel: +48 (0)22 573 24 00 **PT – Portugal** Tel: +351 22 999 7360

RO – Romania, Bucharest Tel: +40 21 252 1382

SE – Sweden, Borås Tel: +46 (0)8 59 79 50 00

SL – Slovenia, Novo Mesto Tel: +386 7 337 6649

TR – Turkey, Istanbul Tel: +90 216 4997081

UK – United Kingdom, Warwick Tel: +44 (0)1926 317 878

ZA – South Africa, Kempton Park Tel: +27 (0)11 961 0700

North America

CA – Canada, Milton, Ontario Tel: +1 905 693 3000

US – USA, Cleveland Tel: +1 216 896 3000

Asia Pacific

AU – Australia, Castle Hill Tel: +61 (0)2-9634 7777

CN – China, Shanghai Tel: +86 21 2899 5000

HK – Hong Kong Tel: +852 2428 8008

IN – India, Mumbai Tel: +91 22 6513 7081-85

JP – Japan, Tokyo Tel: +81 (0)3 6408 3901

KR – South Korea, Seoul Tel: +82 2 559 0400

MY – Malaysia, Shah Alam Tel: +60 3 7849 0800

NZ – **New Zealand,** Mt Wellington Tel: +64 9 574 1744

SG – Singapore Tel: +65 6887 6300

TH – Thailand, Bangkok Tel: +662 186 7000 European Product Information Centre Free phone: 00 800 27 27 5374 (from AT, BE, CH, CZ, DE, DK, EE, ES, FI, FR, IE, IL, IS, IT, LU, MT, NL, NO, PL, PT, RU, SE, SK, UK, ZA)

© 2022 Parker Hannifin Corporation



Parker Hannifin Manufacturing Ltd. Instrumentation Products Division, Europe Riverside Road Barnstaple EX31 1NP United Kingdom phone 0044 1271 313131 www.parker.com/ipd

Parker Hannifin Corporation Instrumentation Products Division 1005 A Cleaner Way Huntsville AL 35805 USA phone 001 (256) 881 2040 www.parker.com/ipd

4190-HYD 14.11.22

BR – Brazil, Sao Jose dos Campos Tel: +55 080 0727 5374

Tel: +54 3327 44 4129

AR - Argentina, Buenos Aires

TW - Taiwan, Taipei

Tel: +886 2 2298 8987

South America

CL – **Chile,** Santiago Tel: +56 22 303 9640

MX – Mexico, Toluca Tel: +52 72 2275 4200